
Combination Patient Lift: Active and Passive Hoists

dualo® mini active with uprighting arm active

Side handles on the lifting arm active





dualo® mini

Strong – reliable – economical

The mobile standard and active hoist, dualo® mini, rounds off the aks hoist collection. The dual principle focuses on greater flexibility and freedom of decision. The mini hoist satisfies the requirements of a "large unit"; however, it is more manoeuvrable and "handier" due to its more compact dimensions.

The advantages of the dualo® mini:

- Multi-functionality: optimal use of the versatile functions of a large standard hoist and/or a active hoist, such as lifting, moving and uprighting persons.
- Effortless take-up of persons directly from the floor with dualo mini standard
- Flexibility: easy conversion of the standard hoist to the active hoist (picture 3+1) and vice versa; simplified insert function thanks to stainless steel square tubes
- Freedom of decision: Take your time. For example, if you decide on a standard hoist, you can retrofit the uprighting arm of the active hoist and the corresponding equipment at any time.
- The lifting arm active features additional side handles to offer greater convenience and support (picture 2)
- Economy and effectiveness: lower acquisition costs and high use frequency, demand-oriented use – particularly practical in care facilities as a dual hoist
- Ideal for small rooms and narrow doors
- Highly stable thanks to mechanical spread of the chassis per foot lever, two lockable castors
- Max. load capacity 150 kg

Options and accessories

- Battery pack with separate charging station on the wall
- For dualo® mini active: aks standaid sling with breast loop and aks calf strap (optional)
- For dualo® mini standard: many hoist slings, various spreader bars and hoist scales
- Respective conversion kits for dualo[®] mini active or standard



See dualo® in action.

